



COMPARTMENT STORAGE BOX PSK55000-PA2-4

- For safe marking of still-to-connect wires.
- 50-compartment storage box in impact-resistant plastic for convenient on-site combination marking.
- Perfect overview – allows quick marking on mounting site.
- Transparent lid for visual confirmation of contents.
- Filled with PA2 markers.

INFORMATION

Design

A compartment storage box with 50 removable compartments containing PA2 markers. The PA2 marker is a closed and adjustable marker sleeve for wires still not connected. Its unique profile with spring-action collars covers a wide diameter range.

Material

PA2: Soft PVC.

Characters

PA2: The characters are hot stamped for excellent readability and long-lasting durability.

Refills

Available from the standard Partex product range

Temperature range

PA2: Shape-resistant from -30 °C to +60 °C

PA2 durability

- Flame-proof UL94-V0 @ 3 mm.
- Chemical resistance meeting Partex' testing program.
- Temperature and ageing resistance meeting Partex' testing program.

OVERVIEW

MARKER BOX CONTENTS

Product	Colour	Number/Product
A-Z	Yellow/Black	100
0-9	Yellow/Black	100
- /	Yellow/Black	100
GRD	Yellow-Green/Black	100
+	Red/White	100
-	Blue/White	100
Blank	Yellow	100
L1, L2, L3	Yellow/Black	100
N	Blue/White	100

A	B	C	D	E	F	G	H	I	J
K	L	M	N	O	P	Q	R	S	T
U	V	W	X	Y	Z	-	/	GRD	N
0	1	2	3	4	5	6	7	8	9
L1	L2	L3	-	+	BLANK	EMPTY	EMPTY	EMPTY	EMPTY

Placement in PSK55000-PA2 compartment storage box.

PRODUCT SIZES

Marker Box	Length mm	Width mm	Height mm
PSK55000-PA2-4	410	320	50

Marker	Diameter mm	Area mm ²	Inch	AWG
PA-2	4.0-10.0	~2.5-16.0	.158"-.394"	13-5

ORDERS

ORDERING INFORMATION AND PACKAGING

Article number	Description	Number/package
PA-20004AV40.A	PA YELLOW: A	100x5
PA-20004AV40.B	PA YELLOW: B	100x5
PA-20004AV40.C	PA YELLOW: C	100x5
PA-20004AV40.D	PA YELLOW: D	100x5
PA-20004AV40.E	PA. YELLOW: E	100x5
PA-20004AV40.F	PA YELLOW: F	100x5
PA-20004AV40.G	PA YELLOW: G	100x5
PA-20004AV40.H	PA. YELLOW: H	100x5
PA-20004AV40.I	PA YELLOW: I	100x5
PA-20004AV40.J	PA YELLOW: J	100x5
PA-20004AV40.K	PA YELLOW: K	100x5
PA-20004AV40.L	PA YELLOW: L	100x5
PA-20004AV40.M	PA YELLOW: M	100x5
PA-20004AV40.N	PA YELLOW: N	100x5
PA-20004AV40.O	PA YELLOW: O	100x5
PA-20004AV40.P	PA YELLOW: P	100x5
PA-20004AV40.Q	PA YELLOW: Q	100x5
PA-20004AV40.R	PA YELLOW: R	100x5
PA-20004AV40.S	PA YELLOW: S	100x5
PA-20004AV40.T	PA YELLOW: T	100x5
PA-20004AV40.U	PA YELLOW: U	100x5
PA-20004AV40.V	PA YELLOW: V	100x5
PA-20004AV40.W	PA YELLOW: W	100x5
PA-20004AV40.X	PA YELLOW: X	100x5
PA-20004AV40.Y	PA YELLOW: Y	100x5
PA-20004AV40.Z	PA YELLOW: Z	100x5
PA-20004AV40.-	PA YELLOW: -	100x5
PA-20004AV40./	PA YELLOW: /	100x5
PA-20004AV40.GRD	PA YELLOW-GREEN: GROUND	100x5
PA-20004AV69.N	PA BLUE: N	100x5
PA-20004AV40.0	PA YELLOW: 0	100x5
PA-20004AV40.1	PA YELLOW: 1	100x5
PA-20004AV40.2	PA YELLOW: 2	100x5
PA-20004AV40.3	PA YELLOW: 3	100x5
PA-20004AV40.4	PA YELLOW: 4	100x5
PA-20004AV40.5	PA YELLOW: 5	100x5
PA-20004AV40.6	PA YELLOW: 6	100x5
PA-20004AV40.7	PA YELLOW: 7	100x5
PA-20004AV40.8	PA YELLOW: 8	100x5
PA-20004AV40.9	PA YELLOW: 9	100x5
PA-20006AV40.L1	PA YELLOW: L1	100x5
PA-20006AV40.L2	PA YELLOW: L2	100x5
PA-20006AV40.L3	PA YELLOW: L3	100x5
PA-20004AV69.-	PA BLUE: -	100x5
PA-20004AV29.+	PA RED: +	100x5
PA-20004AN4	PA UNMARKED YELLOW	100x5