


PmodLS1™ Reference Manual

Revised February 13, 2015

This manual applies to the PmodLS1 rev. B

Overview

The Digilent PmodLS1 allows users to receive signals from multiple optical sensors, such as the popular combination of an IR LED with an IR sensor used in line-following robots.



The PmodLS1.

Features include:

- Up to four attached sensors
- An adjustable gain (threshold) for the sensors

1 Functional Description

The PmodLS1 is designed to be used with up to four sensors containing an infrared LED and an infrared-sensitive photo-transistor, such as the IR Proximity Sensor available from Digilent. When using Digilent's sensors, refer to the print on the board indicating the wire color for the correct orientation of the wire. If third-party sensors are used, refer to the board schematic available at www.digilentinc.com for the proper connection of the LED and photo-transistor.

The module uses analog comparators to determine when the infrared detectors have sensed more infrared light than the threshold limit. The sensitivity of the sensors can be adjusted by adjusting the onboard potentiometer.

2 Interfacing with the Pmod

The PmodLS1 communicates with the host board via the GPIO protocol. By the Pmod design, each of the outputs will only send a logic 1 value when its sensor is picking up more optical light than the threshold limit. When the

light level is lower than the threshold limit, the output will instead send a logic 0 value. This style can then be connected to an interrupt within the system board for an ideal usage, although this is not necessary.

Pin Number	Description
1	Sensor S1
2	Sensor S2
3	Sensor S3
4	Sensor S4
5	Ground
6	VCC

Table 1. Pin descriptions.

Any external power applied to the PmodLS1 needs to be between 2.7V and 5.5V to ensure that no internal components on the Pmod are damaged. Digiilent recommends operating this Pmod at 3.3V.

3 Physical Dimensions

The pins on the pin header are spaced 100 mil apart. The PCB is 1.375 inches long on the sides parallel to the pins on the pin header and 0.8 inches long on the sides perpendicular to the pin header.